



GE LOGIQ 5 PRO / PW / CW / CFM / M / EKG

SKU: V082013

Applications

- Abdominal
- Obstetrical
- Gynecological
- Cardiac
- Musculoskeletal
- Vascular
- Urological
- Small Parts and Superficial
- Pediatric and Neonatal
- Transcranial

Dimensions and Weight

- Height : selectable in factory 1380mm(54") or 1450mm(57")
- Width: 52 cm (20")
- Depth: 99 cm (39")
- Weight : approx. 170 kg (375 lb.)

Electrical Power

- Voltage : 100~120 Vac or 220~240 Vac
- Frequency : 50/60Hz
- Power : Max. 1250 VA with Built-in and On-Board Peripherals
- Maximum Thermal Output : 4250 BTU/hr.

Operator Keyboard

- Keyboard Width : 520mm
- Keyboard Height : 830 or 900mm



- Alphanumeric Keyboard
- Interactive Back-Lighting
- Indicator Lights Identify Activated Keys
- Integrated Recording Keys for Remote Control of Up to 4 Peripheral Devices and **DICOM Devices**
- 8 TGC Pods, with Re-mapping Functionality at Any Depth

Console Design

- 3 active probe ports
 - Integrated hard drive (80 GB)
 - Integrated CD-R/W drive
 - On-board storage for peripherals - B/W-printer, color printer, VCR
 - Wheels - Wheel diameter : Front/Rear : 150mm
- 4 rotating flexible wheels with protection cover
- Integrated locking mechanism that provides rolling lock and optional caster swivel lock
- Probe Holders, Removable for Cleaning and Washing with Integrated Cable

Management

- Gel Holder, Removable for Cleaning and Washing
- Air Filters, Easily Removable
- Rear Storage Cover for Peripheral Connectors and Cables
- Rear Handle

Monitor

- 15" non-interlaced, High-Resolution
- SVGA format - Display size : 800x600 - Recording area : 640x480
- Tilt/Rotate adjustable - Tilt angle : up/down 15°/10° - Rotate angle : right/left 90°
- Height Selectable in factory (with keyboard) : 1238mm to 1308mm at center of monitor
- Digital Brightness/Contrast Adjustment



- Integrated high-fidelity speakers
- Integrated microphone
- Integrated Task Light

Mwst. wird gesondert ausgewiesen

Sehr gepflegt

Im guten gebrauchten Zustand

Artikel-Standort. Hamburg

www.mtc-hamburg.com

info@mtc-hamburg.com

0049 40 18 20 79 03

0049 176 205 800 86

fax.0049 40 65 86 33 64



Categories: [Ultraschall](#) / [Doppler](#) / [Sonden](#)
[/Zubehör](#)

PRODUKTBESCHREIBUNG

Applications

- Abdominal
- Obstetrical
- Gynecological
- Cardiac
- Musculoskeletal
- Vascular
- Urological
- Small Parts and Superficial
- Pediatric and Neonatal
- Transcranial



Dimensions and Weight

- Height : selectable in factory 1380mm(54") or 1450mm(57")
- Width: 52 cm (20")
- Depth: 99 cm (39")
- Weight : approx. 170 kg (375 lb.)

Electrical Power

- Voltage : 100~120 Vac or 220~240 Vac
- Frequency : 50/60Hz
- Power : Max. 1250 VA with Built-in and On-Board Peripherals
- Maximum Thermal Output : 4250 BTU/hr.

Operator Keyboard

- Keyboard Width : 520mm
- Keyboard Height : 830 or 900mm
- Alphanumeric Keyboard
- Interactive Back-Lighting
- Indicator Lights Identify Activated Keys
- Integrated Recording Keys for Remote Control of Up to 4 Peripheral Devices and **DICOM Devices**
- 8 TGC Pods, with Re-mapping Functionality at Any Depth

Console Design

- 3 active probe ports
 - Integrated hard drive (80 GB)
 - Integrated CD-R/W drive
 - On-board storage for peripherals - B/W-printer, color printer, VCR
 - Wheels - Wheel diameter : Front/Rear : 150mm
- 4 rotating flexible wheels with protection cover
- Integrated locking mechanism that provides rolling lock and optional caster swivel lock
- Probe Holders, Removable for Cleaning and Washing with Integrated Cable



Management

- Gel Holder, Removable for Cleaning and Washing
- Air Filters, Easily Removable
- Rear Storage Cover for Peripheral Connectors and Cables
- Rear Handle

Monitor

- 15" non-interlaced, High-Resolution
- SVGA format - Display size : 800x600 - Recording area : 640x480
- Tilt/Rotate adjustable - Tilt angle : up/down 15°/10° - Rotate angle : right/left 90°
- Height Selectable in factory (with keyboard) : 1238mm to 1308mm at center of monitor
- Digital Brightness/Contrast Adjustment
- Integrated high-fidelity speakers
- Integrated microphone
- Integrated Task Light

Mwst. wird gesondert ausgewiesen

Sehr gepflegt

Im guten gebrauchten Zustand

Artikel-Standort. Hamburg

www.mtc-hamburg.com

info@mtc-hamburg.com

0049 40 18 20 79 03

0049 176 205 800 86

fax.0049 40 65 86 33 64

ZUSÄTZLICHE INFORMATIONEN



GALLERIE

